

FleXbus HCBC Plate with PE Connection, 12.5 mm Hole 1, 18.5 mm Hole 2

Data Solutions

KATALOGOVÉ ČÍSLO

FLEXPLATE100PE



CERTIFICATIONS



VLASTNOSTI

Rigid tinned copper part provides strong electrical contact to maintain braid expansion during compression

HCBC Plate allows FleXbus Conductor insulation to overlap the connection palm

HCBC Plate with PE connection allows conductor to be added to interconnect neutral and ground/earth

Tinned copper allows for copper or aluminum conductor connections

Installs quickly and easily

RoHS compliant

VLASTNOSTI PRODUKTU

Article Number: 508183

Materiál: Copper

Povrchová úprava: Tinned

A: 115mm

B: 100mm

C: 45mm

D: 51mm

E: 70mm

Hole Size 1 (HS1): 12.5mm

Hole Size 2 (HS2): 18.5mm

Thickness (T): 5mm


Conductor Size: 960 mm²; 1280 mm²; 1810 mm²

Unit Weight: 0.71kg

DALŠÍ PODROBNOSTI O PRODUKTU

It is mandatory to use the HCBC Clamp associated with the HCBC Plate for proper Flexbus Conductor connection.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE