

# Cable to Web of Rail Complete Welder, Power, 85-141 lb T-Rail, 250 kcmil Ropelay, Right Hand

## Data Solutions

### KATALOGOVÉ ČÍSLO

**PBWT202WRH**



### VLASTNOSTI

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Includes mold cleaner and flint ignitor

### VLASTNOSTI PRODUKTU

Materiál: Graphite; Ocel; Thermoplastic

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: W

Conductor Size: 250 kcmil Ropelay

Conductor Outer Diameter, Nominal: 19.05mm

Welder Style: T20

Orientation: Right Hand

Mold Only: No

Replacement Mold: PBW2WRH

Welding Material: PB115, Sold Separately

Handle Clamp: C105C, Sold Separately

## UPOZORNĚNÍ

---

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**