

Cable to Web of Rail Complete Welder, Power, 85-141 lb T-Rail, 500 kcmil Ropelay, Right Hand

Data Solutions

KATALOGOVÉ ČÍSLO

PBWT203SRH



VLASTNOSTI

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Includes mold cleaner and flint ignitor

VLASTNOSTI PRODUKTU

Materiál: Graphite; Ocel; Thermoplastic

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: W

Conductor Size: 500 kcmil Ropelay

Conductor Outer Diameter, Nominal: 26.42mm

Welder Style: T20

Orientation: Right Hand

Mold Only: No

Replacement Mold: PBW3SRH

Welding Material: PB250, Sold Separately

Handle Clamp: C105C, Sold Separately

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE