

# Compression Straight Lug, Standard, 2/0 Stranded, 70 mm<sup>2</sup> Stranded, 13 mm Hole

## Data Solutions

### KATALOGOVÉ ČÍSLO

---

**RKS7012T**



### VLASTNOSTI

---

Tin plated for corrosion prevention

Annealed copper eases the crimping operation

Optimized sizes to the most efficient electrical conductivity

Best mechanical behavior (vibration/pull-out); DIN EN 61373 Class 1B "Railway Applications"

Markings on barrel for crimping

Consistent material thickness, precise diameter and accurate cable fit; DIN46235

### VLASTNOSTI PRODUKTU

---

Article Number: 716656

Materiál: Copper

Povrchová úprava: Tinned

Lug/Connector Type: Standard

Conductor Size: 2/0 Stranded; 70 mm<sup>2</sup> Stranded

Hole Size (HS): 13mm

Length (L): 59mm

Width (W): 23mm

Tool/Die Type: M2M or M2H/RKM2; M3H or M3B/RKM3; MLB/RKML

## DIAGRAMS

---



## UPOZORNĚNÍ

---

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte**