


Joint Bond T6 Complete Welder Pair, Signal, Head Free Bond Terminal Style, 3/16" Bondstrand

Data Solutions

KATALOGOVÉ ČÍSLO

SBHFT6C



VLASTNOSTI

Complete welder assembly provides a convenient means of attaching jumper bonds to the head of the rail, across the joint

Connection is made within the confines of the splice bar

Includes mold cleaner

VLASTNOSTI PRODUKTU

Materiál: Ocel; Graphite; Thermoplastic

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: Head Free

Conductor Size: 3/16" Bondstrand

Conductor Outer Diameter, Nominal: 4.76mm

Bond Length: 190.5mm

Welder Style: T6

Mold Only: No

Replacement Mold: SBS925M

Welding Material: SB32, Sold Separately

Frame: SBS925F, Sold Separately

Bond Clip: S2659 x 2, Sold Separately

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRachte