

Single Temperature and Humidity Sensor

Data Solutions

KATALOGOVÉ ČÍSLO

EA9103



Single Temperature and Humidity Probe Sensor for nVent SCHROFF RackPower PDU's.

VLASTNOSTI

Single Temperature and Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +/- 2 %

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy +/- 5 %

VLASTNOSTI PRODUKTU

Product Type: Sensor

Works With: RackPower

Výška: 270mm

Množství v balení: 1

Plug Type: RJ45

Produktová řada: Enlogic

Removable Input Cable: No

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE