

Basic PDU, EB0317-A, 230 VAC, 1-PH, 16 A

Data Solutions

KATALOGOVÉ ČÍSLO

EB0317-A



Modular, compact PDU. Ultra-Low Profile Design

VLASTNOSTI

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

VLASTNOSTI PRODUKTU

Produktová řada: Enlogic

Typ: Basic PDU

Product Type: Socket Strip

Typ zásuvky: (10) C13; (1) C19

Socket Quantity: 11

Barva: Black

Circuit Breaker: 16 A, 1-pole, Hy-Mag

Switched Outlets: No

Circuit Breaker Quantity: 0

Input Cable Location: Front Feed

Input Voltage: 100 – 240V

Phase: 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 3.68 kVA

Output Voltage: 100 – 240VAC

Amperage (Derated Amperage): 20 A (16 A) North America; 16 A International

Plug Type: C20

Rack Units: 0U

Removable Input Cable: Yes

Metering Type: None

Množství v balení: 1

Input Cable Length: 0m

DALŠÍ PODROBNOSTI O PRODUKTU

Please order bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE