

# CompacPRO Front Panel

The front panel for the CompacPRO Cases is bolted to the front frame of the case.



## CERTIFICATIONS



## VLASTNOSTI

The front panel is bolted to the front frame of the enclosure

## SPECIFIKACE

<b>Materiál:</b>	Hliník
<b>Povrchová úprava:</b>	Anodized
<b>Accessory Type:</b>	Front panel
<b>Product Type:</b>	Front Panel

Table 1/2

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Front Finish	Rear Finish
30823-227	4U	63HP	3mm	1	Anodized	Anodized
30823-209	2U	42HP	3mm	1	Anodized	Anodized
30823-224	3U	63HP	3mm	1	Anodized	Anodized
30823-284	6U	84HP	3mm	1	Anodized	Anodized
30823-254	3U	28HP	3mm	1	Anodized	Anodized
30823-272	4U	84HP	3mm	1	Anodized	Anodized

Katalogové číslo	Rack Height	Rack Width	Hloubka	Množství v balení	Front Finish	Rear Finish
30823-269	4U	42HP	3mm	1	Anodized	Anodized
30823-257	3U	42HP	3mm	1	Anodized	Anodized
30823-260	3U	84HP	3mm	1	Anodized	Anodized
30823-215	2U	84HP	3mm	1	Anodized	Anodized
30823-230	6U	63HP	3mm	1	Anodized	Anodized

Table 2/2

Katalogové číslo	Treated Edges	EMC Shielding	Výška	Šířka
30823-227	No	No	172.9mm	345.4mm
30823-209	No	No	84mm	238.7mm
30823-224	No	No	128.4mm	345.4mm
30823-284	No	No	261.8mm	452.1mm
30823-254	No	No	128.4mm	167.5mm
30823-272	No	No	172.9mm	452.1mm
30823-269	No	No	172.9mm	238.7mm
30823-257	No	No	128.4mm	238.7mm
30823-260	No	No	128.4mm	452.1mm
30823-215	No	No	84mm	452.1mm
30823-230	No	No	261.8mm	345.4mm

## DALŠÍ PODROBNOSTI O PRODUKTU

Assembly Kit to fix one rear and one front panel is included with the case.

## UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

### North America

All locations

+1.763.422.2661

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

[nvent.com/schroff](https://nvent.com/schroff)



Naše portfolio silných značek:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**