

Inpac Front Panel, Bottom-Hinged

The bottom hinged front panel can be combined with the Inpac cases.



CERTIFICATIONS



VLASTNOSTI

The bottom hinged front panel can be combined with the Inpac cases

SPECIFIKACE

Hloubka:	2.5mm
Materiál:	Hliník
Povrchová úprava:	Anodized
Accessory Type:	Front panel
Product Type:	Front Panel

Table 1/2

Katalogové číslo	Rack Height	Množství v balení	Front Finish	Rear Finish	Treated Edges	EMC Shielding
30828-085	2U	1	Anodized	Anodized	No	No
30828-097	6U	1	Anodized	Anodized	No	No
30828-091	4U	1	Anodized	Anodized	No	No
30828-088	3U	1	Anodized	Anodized	No	No

Table 2/2

Katalogové číslo	Výška	Šířka
30828-085	76mm	437mm
30828-097	253.8mm	437mm
30828-091	165mm	437mm
30828-088	120.5mm	437mm

DALŠÍ PODROBNOSTI O PRODUKTU

Please order hinge for front panel separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE