

LED Lights for Cabinets



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

CERTIFICATIONS



VLASTNOSTI

Power cable for LED light mounting into cabinet

Lights can be easily mounted vertically or horizontally

Simple through-wiring based on a plug-and-play system

SPECIFIKACE

Product Type: Light

Table 1/2

Katalogové číslo	Accessory Type	Stupeň krytí	Množství v balení	Barva	Povrchová úprava	Typ
57274	Lights	IP20	1	Black	Smooth Matte	Cabinet Light, Terminal Block
57275	Lights	IP20	2		Smooth Matte	Cabinet Light, Magnet
60130-114	Lights	IP20	1		Smooth	Connection Cable
57265	Lights	IP20	1	Black	Smooth Matte	Cabinet Light
57272	Lights	IP20	1	Black	Smooth	Connection Cable

Katalogové číslo	Accessory Type	Stupeň krytí	Množství v balení	Barva	Povrchová úprava	Typ
57273	Lights	IP20	1	Black	Smooth	Connection Cable

Table 2/2

Katalogové číslo	Typ připojení	Light Output	Rated Current	Hmotnost	Certifications
57274	Infeed, Trough-Wiring, 2-Pole		16A	0.07kg	RoHS
57275				0.08kg	RoHS
60130-114	Infeed, Trough-Wiring, 2-Pole		10A	0.083kg	RoHS, EAC
57265	Infeed, Trough-Wiring, 2-Pole	550lm		0.24kg	CE, RoHS
57272	Infeed, Trough-Wiring, 2-Pole		10A	0.3kg	RoHS
57273	Infeed, Trough-Wiring, 2-Pole		10A	0.3kg	RoHS

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE