

PropacPRO Case Design Elements

To individualize the PropacPRO case design. The elements will be screwed from the rear side of the die cast frame.



CERTIFICATIONS



VLASTNOSTI

To individualize the case design

Available in 3 forms and two colors

SPECIFIKACE

| | |
|--------------------------|----------------|
| Materiál: | Hliník |
| Povrchová úprava: | Anodized |
| Works With: | Cases |
| Product Type: | Corner Profile |
| Produktová řada: | PropacPRO |

Table 1/1

| Katalogové číslo | Rack Width | Typ | Kód barvy | Barva |
|------------------|------------|----------|-----------|----------------|
| 20850-299 | 42HP | Rounded | RAL 5007 | Brilliant Blue |
| 20850-196 | 42HP | Triangle | RAL 7035 | Light Grey |
| 20850-190 | 42HP | Squared | RAL 7035 | Light Grey |
| 20850-315 | 42HP | Squared | RAL 5007 | Brilliant Blue |

| Katalogové číslo | Rack Width | Typ | Kód barvy | Barva |
|------------------|------------|----------|-----------|----------------|
| 20850-184 | 42HP | Rounded | RAL 7035 | Light Grey |
| 20850-331 | 42HP | Triangle | RAL 5007 | Brilliant Blue |
| 20850-185 | 63HP | Rounded | RAL 7035 | Light Grey |
| 20850-191 | 63HP | Squared | RAL 7035 | Light Grey |
| 20850-197 | 63HP | Triangle | RAL 7035 | Light Grey |
| 20850-316 | 63HP | Squared | RAL 5007 | Brilliant Blue |
| 20850-332 | 63HP | Triangle | RAL 5007 | Brilliant Blue |
| 20850-300 | 63HP | Rounded | RAL 5007 | Brilliant Blue |
| 20850-192 | 84HP | Squared | RAL 7035 | Light Grey |
| 20850-198 | 84HP | Triangle | RAL 7035 | Light Grey |
| 20850-186 | 84HP | Rounded | RAL 7035 | Light Grey |
| 20850-317 | 84HP | Squared | RAL 5007 | Brilliant Blue |
| 20850-333 | 84HP | Triangle | RAL 5007 | Brilliant Blue |
| 20850-301 | 84HP | Rounded | RAL 5007 | Brilliant Blue |

DALŠÍ PODROBNOSTI O PRODUKTU

Size 28 HP and further colors available on request.

Cannot be combined with front hood.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE