

Socket Strip With 2 Supply Cable, 3-Phase

Modular, compact PDU with two power cord inputs that can be connected to an A and B power feed. Space saving design in one chassis.



CERTIFICATIONS



VLASTNOSTI

Horizontal and vertical assembly possible

Two connector cables (halved in direction of length), 3 m (with open end), 2 x 3 phase, 400 VAC (red, black, white area)

Socket strips can be rotated in all directions (in 90° increments) during installation

Mounting height 1 U

SPECIFIKACE

Length:	1848.5mm
Materiál:	Hliník; Polyamide
Barva:	Grey; Black; Red
Product Type:	Socket Strip

Table 1/2

Katalogové číslo	Typ zásuvky	Socket Quantity	Switched Outlets	Napětí střídavé	Množství v balení	Hloubka
60110-287	IEC C13	48	No	400V	1	44mm
60110-286	IEC C13, SCHUKO	36	No	400V	1	44mm

Table 2/2

Katalogové číslo	Povrchová úprava	Výška
60110-287	Anodized	44mm
60110-286	Anodized	44mm

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Naše portfolio silných značek:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE