

Socket Strip, SCHUKO, With Wieland® Input



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



VLASTNOSTI

Installation height 1 U

Output via SCHUKO sockets

Input via Wieland® GST 18 plug

Socket strips can be rotated through all four directions (in 90° increments) during installation

Horizontal or vertical mounting

In accordance with DIN 57620

SPECIFIKACE

Length:	438.5mm
Materiál:	Hliník; Polyamide
Product Type:	Socket Strip

Table 1/2

Katalogové číslo	Typ zásuvky	Socket Quantity	Switched Outlets	Napětí střídavé	Function	Množství v balení
60110-354	SCHUKO	6	No	230V	Overcurrent Protection	1

Katalogové číslo	Typ zásuvky	Socket Quantity	Switched Outlets	Napětí střídavé	Function	Množství v balení
60110-353	SCHUKO	6	No	230V	Overcurrent Protection	1
60110-343	SCHUKO	8	No	230V		1
60110-352	SCHUKO	6	No	230V	Overcurrent Protection	1
60110-345	SCHUKO	8	No	230V		1
60110-344	SCHUKO	8	No	230V		1

Table 2/2

Katalogové číslo	Barva	Hloubka	Povrchová úprava
60110-354	Red	44mm	Anodized
60110-353	Black	44mm	Anodized
60110-343	Grey	44mm	Anodized
60110-352	Grey	44mm	Anodized
60110-345	Red	44mm	Anodized
60110-344	Black	44mm	Anodized

DALŠÍ PODROBNOSTI O PRODUKTU

Please order bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE