

Socket Strip, UTE, With Wieland® Input



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



VLASTNOSTI

Input via Wieland® GST 18 plug

Socket strips can be rotated through all four directions (in 90° increments) during fitting

Output via UTE sockets

Horizontal or vertical mounting

Installation height 1 U

In accordance with NFC 61-303

SPECIFIKACE

| | |
|----------------------|-------------------|
| Length: | 438.5mm |
| Materiál: | Hliník; Polyamide |
| Product Type: | Socket Strip |

Table 1/2

| Katalogové číslo | Typ zásuvky | Socket Quantity | Switched Outlets | Napětí střídavé | Function | Množství v balení |
|------------------|-------------|-----------------|------------------|-----------------|------------------------|-------------------|
| 60110-357 | UTE | 6 | No | 230V | Overcurrent Protection | 1 |

| Katalogové číslo | Typ zásuvky | Socket Quantity | Switched Outlets | Napětí střídavé | Function | Množství v balení |
|------------------|-------------|-----------------|------------------|-----------------|------------------------|-------------------|
| 60110-356 | UTE | 6 | No | 230V | Overcurrent Protection | 1 |
| 60110-346 | UTE | 8 | No | 230V | | 1 |
| 60110-355 | UTE | 6 | No | 230V | Overcurrent Protection | 1 |
| 60110-348 | UTE | 8 | No | 230V | | 1 |
| 60110-347 | UTE | 8 | No | 230V | | 1 |

Table 2/2

| Katalogové číslo | Barva | Hloubka | Povrchová úprava |
|------------------|-------|---------|------------------|
| 60110-357 | Red | 44mm | Anodized |
| 60110-356 | Black | 44mm | Anodized |
| 60110-346 | White | 44mm | Anodized |
| 60110-355 | White | 44mm | Anodized |
| 60110-348 | Red | 44mm | Anodized |
| 60110-347 | Black | 44mm | Anodized |

DALŠÍ PODROBNOSTI O PRODUKTU

Please order mounting bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Naše portfolio silných značek:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE