

# Cable Spool

## Data Solutions



### CERTIFICERINGER



### FUNKTIONER

Cut to length as needed

Pre-stretched restraint cable

Certified chemically compatible with CPVC piping systems

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

### SPECIFIKATIONER

**Finish:** Pregalvanized; Painted

**Materiale:** Stål

Table 1/1

| Katalognummer | Artikelnummer | Brace Size | Diameter | Cable Length | UL Listed Load | Farve |
|---------------|---------------|------------|----------|--------------|----------------|-------|
| CSB12CBL      | 402190        | #12        | 2.4mm    | 76.2m        | 1859N          | Red   |
| CSB18CBL      | 402191        | #18        | 3.2mm    | 76.2m        | 3434N          | White |
| CSB36CBL      | 402192        | #36        | 4.8mm    | 76.2m        | 8490N          | Blue  |

## YDERLIGERE PRODUKTOPLYSNINGER

Cable is powder coated.

FBC™ System Compatible indicates that this product has been tested, and is monitored on an ongoing basis, to assure its chemical compatibility with FlowGuard Gold®, BlazeMaster® and Corzan® piping systems and products made with TempRite® Technology.™ “The FBC System Compatible Logo, FBC™, FlowGuard Gold®, BlazeMaster®, Corzan®, and TempRite® are trademarks of Lubrizol Advanced Materials, Inc. or its affiliates.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**