

Low Voltage Insulators, Metric Thread, 60 mm, 55 mm Hex Width, M8 Thread

Data Solutions

KATALOGNUMMER

ISOTP60M8



CERTIFICERINGER



FUNKTIONER

Halogen free

High resistance to leakage current

Great stability of electrical and mechanical parameters

Fiberglass reinforced

UL® Recognized in E125470 and evaluated for dielectric withstand rating of 1,500 VAC/DC

RoHS compliant

PRODUKTEGENSKABER

Artikelnummer: 548600

Materiale: Stål; Glass Fibre Reinforced Polyamide

Finish: Electrogalvanized

Working Temperature: -40 to 130°C

Flammability Rating: UL® 94V-0

Complies With: IEC® 60695-2-11 (Glow Wire Test 960 °C)

Dielectric Strength, IEC 61439.1: 3500 VAC @ 1 min

Dielectric Strength, UL: 1500

Insulation Voltage: 1000; 1500

Height (H): 60mm

Hex Width (W): 55mm

Dybde (D): 63mm

Thread Size (TS): M8

Thread Depth (TD): 15mm

Diameter (Ø): 44mm

Static Load 1 (F1): 2200daN

Static Load 2 (F2): 1000daN

Unit Weight: 0.19kg

YDERLIGERE PRODUKTOPLYSNINGER

Creepage and clearance distances need to be in accordance with the relevant application standard.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE