

# Flat Braided Power Shunt, 500 mm<sup>2</sup>, 400 mm

## Data Solutions

### KATALOGNUMMER

**PBC500X400**



### CERTIFICERINGER



### FUNKTIONER

Ideal for transformer-busduct link

Solid palms can be drilled to fit customer specific designs

Extra flexible power connection and good resistance to vibration

### PRODUKTEGENSKABER

Artikelnummer: 564600

Materiale: Copper

Finish: Tinned

Wire Diameter: 0.15mm

Cross Section: 500mm<sup>2</sup>

ΔT 30 K: 917A

$\Delta T$  50 K: 1216A

Length (L): 400mm

A: 105mm

B: 100mm

C: 11mm

2 Bar Current Coefficient: 1.65

Unit Weight: 2.64kg

## YDERLIGERE PRODUKTOPLYSNINGER

When used in parallel, the two shunts must be spaced with a minimum distance equal to the thickness of the shunt to allow air cooling.

## DIAGRAMS



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**