

# Varistar CP Steel Door, Plain With 3-Point Locking, RAL 7021, 29 U, 1400H 600W, IP55

## Data Solutions

### KATALOGNUMMER

**21630-211**



Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

### FUNKTIONER

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

### PRODUKTEGENSKABER

Rack Height: 29U

Højde: 1400mm

Bredde: 600mm

Pakke mængde: 1

Farve: Black Grey

Farvekode: RAL 7021

Complies With: IEC 61587-1

Finish: Struktur Pulvermaling

Locking Type: 3-Point Locking

Materiale: Stål

Produktfamilie: Varistar CP

Product Type: Cabinet Door

Beskyttelsesgrad: IP55

Type: Steel Door

Works With: Varistar CP

Net Weight: 15.761kg

## YDERLIGERE PRODUKTOPLYSNINGER

---

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

## ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**