

Varistar CP Steel Door, Plain With 3-Point Locking, RAL 7021, 24 U, 1200H 800W, IP55

Data Solutions

KATALOGNUMMER

21630-216



Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

FUNKTIONER

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

PRODUKTEGENSKABER

Rack Height: 24U

Højde: 1200mm

Bredde: 800mm

Pakke mængde: 1

Farve: Black Grey

Farvekode: RAL 7021

Complies With: IEC 61587-1

Finish: Struktur Pulvermaling

Locking Type: 3-Point Locking

Materiale: Stål

Produktfamilie: Varistar CP

Product Type: Cabinet Door

Beskyttelsesgrad: IP55

Type: Steel Door

Works With: Varistar CP

Net Weight: 17.184kg

YDERLIGERE PRODUKTOPLYSNINGER

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE