

Varistar CP Steel Door, Plain With 3-Point Locking, RAL 7021, 38 U, 1800H, 800W, IP20

Data Solutions

KATALOGNUMMER

21630-439



Perforated Varistar CP steel double door with 3-point locking for applications with IP 20 protection.

FUNKTIONER

Steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

PRODUKTEGENSKABER

Rack Height: 38U

Højde: 1800mm

Bredde: 800mm

Pakke mængde: 1

Farve: Black Grey

Farvekode: RAL 7021

Complies With: IEC 61587-1; IEC 61587-3

Finish: Struktur Pulvermaling

Locking Type: 3-Point Locking

Materiale: Stål

Produktfamilie: Varistar CP

Product Type: Cabinet Door

Beskyttelsesgrad: IP20

Type: Steel Door

Works With: Varistar CP

Net Weight: 22.231kg

YDERLIGERE PRODUKTOPLYSNINGER

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer.

Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE