

# Filtered Door for RackChiller In-Row 45

## Data Solutions

### KATALOGNUMMER

---

**24630-188**

The filtered door replaces a standard unfiltered door on the RackChiller In-Row 45 in order to extend the device with air filtering of incoming / warm aisle air. The filter is washable / cleanable with clean water or compressed air.

### FUNKTIONER

---

Filtration according to EN779:2012 Class G2; ISO 16890 Coarse 35%

Replaces standard door of RackChiller In-Row 45

### PRODUKTEGENSKABER

---

Product Type: Air/Liquid Heat Exchanger

Produktfamilie: Varistar CP

Bredde: 300mm

Højde: 2000mm

Farve: Black Grey

Farvekode: RAL 7021

Finish: Struktur Pulvermaling

Materiale: Stål

Net Weight: 11.526kg

Pakke mængde: 1

Rack Height: 42U

### YDERLIGERE PRODUKTOPLYSNINGER

---

Works only with Varistar LHX+ 45 In-Rack and RackChiller In-Row 45

### ADVARSEL

---

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug,

fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**