

19" Front Panel, 7 U, 3 mm, Al, RAL7035

Data Solutions

KATALOGNUMMER

30118-306



Front panels made of Aluminum.

CERTIFICERINGER



FUNKTIONER

Aluminum, 4 or 3 mm thick, with Anodized or Painted finish

PRODUKTEGENSKABER

Rack Height: 7U

Dybde (D): 3mm

Accessory Type: Front panel

Mounting: Screw-on Front

Finish: Struktur Pulvermaling

Front Finish: Painted

Pakke mængde: 1

Farvekode: RAL 7035

Højde (H): 310.3mm

Product Type: Front Panel

Type: 19" Front Panel

Gross Weight: 1.245kg

Please order 19" assembly kit separately.

Technical drawing of a rectangular plate. The overall width is 483 and the overall height is H. The plate has four holes along each of the long vertical edges. The distance from the left edge to the center of the first hole is g. The distance between the centers of adjacent holes is 465. On the right edge, the distance from the top edge to the center of the first hole is X1, and the distance between the centers of the two middle holes is X2.

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE