

LED Light Connection Cable With IEC 60320 C18 - GST15 Connectors for AC

Data Solutions

KATALOGNUMMER

60130-114



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

CERTIFICERINGER



FUNKTIONER

Power cable for LED light mounting into cabinet

Lights can be easily mounted vertically or horizontally

Simple through-wiring based on a plug-and-play system

PRODUKTEGENSKABER

Accessory Type: Lights

Beskyttelsesgrad: IP20

Length: 500mm

Pakke mængde: 1

Finish: Smooth

Product Type: Light

Type: Connection Cable

Tilslutningstype: Infeed; Trough-Wiring; 2-Pole

Nominal spænding: 250V

Driftstemperatur: 60°C min

Rated Current: 10A

Vægt: 0.083kg

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE