

Enlogic Basic PDU

Data Solutions



The Basic PDU is a cost-effective, reliable power distribution solution. Premium hydraulic-magnetic circuit breakers operate consistently in high-temperature environments. The Basic PDU offers advanced features, such as color-coded locking IEC outlets, a slim chassis design, and toolless mounting backed by a 5-year hassle-free warranty.

FUNKTIONER

Black Powder Coated Chassis

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information.

SPECIFIKATIONER

Table 1/6

Katalognummer	Produktfamilie	Type	Product Type	Stiktype	Socket Quantity	Farve
EB0860	Enlogic	Basic PDU	Socket Strip	(24) C13/C15, (24) C13/C15/C19/C21	48	Black
EB09JA	Enlogic	Basic PDU	Socket Strip	(18) C13/C15, (18) C13/C15/C19/C21	36	Black
EB0360	Enlogic	Basic PDU	Socket Strip	(16) C13/C15	20	Black

Table 2/6

Katalognummer	Switched Outlets	Cable Length	Circuit Breaker	Power Rating	Circuit Breaker Quantity	Interrupt Rating
EB0860	No	3000mm	20 A, 1-pole, Hy-MagA	17.3 kVA North America, 22.1 kVA International	6	

Katalognummer	Switched Outlets	Cable Length	Circuit Breaker	Power Rating	Circuit Breaker Quantity	InterruptRating
EB09JA	No	1800mm	20 A, 1-pole, Hy-MagA	34.6 kVA North America, 43.5 kVA International	12	
EB0360	No	3000mm	16 A, 1-pole, Hy-Mag	7.4 kVA	2	5kAIC

Table 3/6

Katalognummer	Nominal Power Output	Nominal spænding	Number of Output Voltages	Antal faser	On/Off Switch Included	Amperage (Derated Amperage)
EB0860	230VAC	415V			No	30 A (24 A) North America, 32 A International
EB09JA	230VAC	415V	36		No	60 A (48 A) North America, 63 A International
EB0360	230VAC	230V	20	1	No	32 A

Table 4/6

Katalognummer	Output Voltage	Rack Units	Plug Type	Metering Type	Removable Input Cable	Materiale
EB0860	208 – 230VAC	0U	IEC 60309 530P6/532P6	None	No	Stål
EB09JA	208 – 230VAC	0U	IEC 60309 560P6/563P6	None	No	Stål
EB0360	230VAC	0U	IEC 60309 332P6 (IP44)	None	No	Stål

Table 5/6

Katalognummer	Finish	Højde	Bredde	Dybde	Vægt	Pakke mængde
EB0860	Struktur Pulvermaling	1490mm	56mm	55mm		1
EB09JA	Struktur Pulvermaling	965mm	114mm	75mm		1
EB0360	Struktur Pulvermaling	817mm	52mm	53mm	3.6kg	1

Table 6/6

Katalognummer	Input Cable Length
---------------	--------------------

EB0860	3m
EB09JA	1.8m
EB0360	3m

YDERLIGERE PRODUKTOPLYSNINGER

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE