

LED Lights for Cabinets

Data Solutions



The enclosure light provides a compact and flexible solution, and offers fast, easy assembly and installation. For mounting flexibility, the LED light can be fastened to the enclosure with screws or quickly attached to any flat steel surfaces with optional magnetic kits. A motion sensor is also available.

CERTIFICERINGER



FUNKTIONER

Power cable for LED light mounting into cabinet

Lights can be easily mounted vertically or horizontally

Simple through-wiring based on a plug-and-play system

SPECIFIKATIONER

Product Type: Light

Table 1/2

Katalognummer	Accessory Type	Beskyttelsesgrad	Pakke mængde	Farve	Finish	Type
57274	Lights	IP20	1	Black	Smooth Matte	Cabinet Light, Terminal Block
57275	Lights	IP20	2		Smooth Matte	Cabinet Light, Magnet
60130-114	Lights	IP20	1		Smooth	Connection Cable

Katalognummer	AccessoryType	Beskyttelsesgrad	Pakke mængde	Farve	Finish	Type
57265	Lights	IP20	1	Black	Smooth Matte	Cabinet Light
57272	Lights	IP20	1	Black	Smooth	Connection Cable
57273	Lights	IP20	1	Black	Smooth	Connection Cable

Table 2/2

Katalognummer	Tilslutningstype	Light Output	Rated Current	Vægt	Certificeringer
57274	Infeed, Trough-Wiring, 2-Pole		16A	0.07kg	RoHS
57275				0.08kg	RoHS
60130-114	Infeed, Trough-Wiring, 2-Pole		10A	0.083kg	RoHS, EAC
57265	Infeed, Trough-Wiring, 2-Pole	550lm		0.24kg	CE, RoHS
57272	Infeed, Trough-Wiring, 2-Pole		10A	0.3kg	RoHS
57273	Infeed, Trough-Wiring, 2-Pole		10A	0.3kg	RoHS

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE