

# Varistar CP Glazed Door With 1-Point Locking

## Data Solutions



Varistar CP Glass Door Single Point Locking for IP 20 applications.

### FUNKTIONER

St, 1.5 mm

Security glass, 6 mm

Key lock cover

Opening angle 180°

### SPECIFIKATIONER

**Product Type:** Cabinet Door

**Materiale:** Stål; Glass

**Beskyttelsesgrad:** IP20

Table 1/2

| Katalognummer | Rack Height | Højde  | Bredde | Locking Type         | Pakke mængde | Farve      |
|---------------|-------------|--------|--------|----------------------|--------------|------------|
| 21630-392     | 24U         | 1200mm | 600mm  | Single Point Locking | 1            | Black Grey |
| 21630-484     | 29U         | 1400mm | 800mm  | Single Point Locking | 1            | Black Grey |
| 21630-483     | 29U         | 1400mm | 600mm  | Single Point Locking | 1            | Black Grey |

| Katalognummer | Rack Height | Højde  | Bredde | Locking Type         | Pakke mængde | Farve      |
|---------------|-------------|--------|--------|----------------------|--------------|------------|
| 21630-485     | 33U         | 1600mm | 600mm  | Single Point Locking | 1            | Black Grey |
| 21630-018     | 47U         | 2000mm | 800mm  | Single Point Locking | 1            | Black Grey |
| 21630-019     | 47U         | 2200mm | 800mm  | Single Point Locking | 1            | Black Grey |
| 21630-482     | 24U         | 1200mm | 800mm  | Single Point Locking | 1            | Black Grey |
| 21630-486     | 33U         | 1600mm | 800mm  | Single Point Locking | 1            | Black Grey |
| 21630-481     | 24U         | 1200mm | 600mm  | Single Point Locking | 1            | Black Grey |
| 21630-487     | 38U         | 1800mm | 600mm  | Single Point Locking | 1            | Black Grey |
| 21630-399     | 38U         | 1800mm | 800mm  | Single Point Locking | 1            | Black Grey |
| 21630-488     | 38U         | 1800mm | 800mm  | Single Point Locking | 1            | Black Grey |
| 21630-017     | 42U         | 2200mm | 600mm  | Single Point Locking | 1            | Black Grey |
| 21630-398     | 38U         | 1800mm | 600mm  | Single Point Locking | 1            | Black Grey |
| 21630-397     | 33U         | 1600mm | 800mm  | Single Point Locking | 1            | Black Grey |
| 21630-492     | 47U         | 2200mm | 800mm  | Single Point Locking | 1            | Black Grey |
| 21630-016     | 42U         | 2000mm | 600mm  | Single Point Locking | 1            | Black Grey |
| 21630-395     | 29U         | 1400mm | 800mm  | Single Point Locking | 1            | Black Grey |
| 21630-491     | 47U         | 2200mm | 600mm  | Single Point Locking | 1            | Black Grey |
| 21630-396     | 33U         | 1600mm | 600mm  | Single Point Locking | 1            | Black Grey |

Table 2/2

| Katalognummer | Rack Height | Højde  | Bredde | Locking Type         | Pakke mængde | Farve      |
|---------------|-------------|--------|--------|----------------------|--------------|------------|
| 21630-489     | 42U         | 2000mm | 600mm  | Single Point Locking | 1            | Black Grey |

| Katalognummer | Rack Height | Højde  | Bredde | Locking Type         | Pakke mængde | Farve      |
|---------------|-------------|--------|--------|----------------------|--------------|------------|
| 21630-490     | 42U         | 2000mm | 800mm  | Single Point Locking | 1            | Black Grey |
| 21630-394     | 29U         | 1400mm | 600mm  | Single Point Locking | 1            | Black Grey |
| 21630-393     | 24U         | 1200mm | 800mm  | Single Point Locking | 1            | Black Grey |

Table 1/2

| Katalognummer | Farvekode | Complies With | Finish                | Type       | Works With  |
|---------------|-----------|---------------|-----------------------|------------|-------------|
| 21630-392     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-484     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-483     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-485     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-018     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-019     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-482     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-486     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-481     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-487     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-399     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-488     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-017     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-398     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |
| 21630-397     | RAL 7021  | IEC 61587-1   | Struktur Pulvermaling | Glass Door | Varistar CP |

| Katalognummer | Farvekode | Complies With | Finish                   | Type       | Works With  |
|---------------|-----------|---------------|--------------------------|------------|-------------|
| 21630-492     | RAL 7021  | IEC 61587-1   | Struktur<br>Pulvermaling | Glass Door | Varistar CP |
| 21630-016     | RAL 7021  | IEC 61587-1   | Struktur<br>Pulvermaling | Glass Door | Varistar CP |
| 21630-395     | RAL 7021  | IEC 61587-1   | Struktur<br>Pulvermaling | Glass Door | Varistar CP |
| 21630-491     | RAL 7021  | IEC 61587-1   | Struktur<br>Pulvermaling | Glass Door | Varistar CP |
| 21630-396     | RAL 7021  | IEC 61587-1   | Struktur<br>Pulvermaling | Glass Door | Varistar CP |

Table 2/2

| Katalognummer | Farvekode | Complies With | Finish                   | Type       | Works With  |
|---------------|-----------|---------------|--------------------------|------------|-------------|
| 21630-489     | RAL 7021  | IEC 61587-1   | Struktur<br>Pulvermaling | Glass Door | Varistar CP |
| 21630-490     | RAL 7021  | IEC 61587-1   | Struktur<br>Pulvermaling | Glass Door | Varistar CP |
| 21630-394     | RAL 7021  | IEC 61587-1   | Struktur<br>Pulvermaling | Glass Door | Varistar CP |
| 21630-393     | RAL 7021  | IEC 61587-1   | Struktur<br>Pulvermaling | Glass Door | Varistar CP |

## YDERLIGERE PRODUKTOPLYSNINGER

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**