

# TCB Threaded Busbar



## CERTIFICERINGER



## FUNKTIONER

Heavy-duty power connection

Circuit breaker, generator and prefabricated power network conductor

Alternative to large and multiple cables

Earth/ground connection

Power distribution

Rounded edges

## SPECIFIKATIONER

**Materiale:** Copper

Table 1/2


Katalognummer	Artikelnummer	Width (W)	Thickness (T)	Length (L)	Thread Size (TS)	Torque (TQ)
TCB12X2-1M	549230	12 mm	2 mm	990mm	M5	1.3 N·m
TCB12X4-1M	550200	12 mm	4 mm	990mm	M5	2 N·m
TCB25X4-1M	549210	25 mm	4 mm	1000mm	M6	4.5 N·m

Katalognummer	Artikelnummer	Width (W)	Thickness (T)	Length (L)	Thread Size (TS)	Torque (TQ)
TCB18X4-1M	549200	18 mm	4 mm	1000mm	M8	11 N·m
TCB12X4-2M	550190	12 mm	4 mm	1985mm	M5	2 N·m
TCB12X5-1M	549220	12 mm	5 mm	990mm	M5	5.5 N·m

Table 2/2

Katalognummer	Artikelnummer	A	Unit Weight
TCB12X2-1M	549230	18 mm	0.3 kg
TCB12X4-1M	550200	18 mm	0.43 kg
TCB25X4-1M	549210	20 mm	0.8 kg
TCB18X4-1M	549200	20 mm	0.6 kg
TCB12X4-2M	550190	18 mm	0.85 kg
TCB12X5-1M	549220	18 mm	0.5 kg

## DIAGRAMS



## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**