

CS480 Wall Joint



CS480 Wall Joint with vertical socket and attaches to a wall or a vertical surface. Arm can be rotated or turned 340 degrees. Cover to facilitate wiring. Maintenance-free bearings.

INDUSTRISTANDARDER

IEC 60529, IP66

FUNKTIONER

Joint can rotate 340 degrees with rotation stop

Torque preset at factory

Gasket and mounting hardware are included

Surface mounting fasteners are not provided

Assembled CS480 HMI Arm System has a max weight load of 89.6 lb. (40.7 kg)

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE