

## Almindelige døre | Gulvskabe, DN



Denne dør erstatter bagpanelet i et gulvskab og giver mulighed for adgang bagfra til udstyr, som er monteret i front, eller mulighed for brug af monteringsplader ryg mod ryg for at øge skabets monteringsplads.

### FUNKTIONER

Beskrivelse: Standarddør udstyret med dobbelt-bit 3 mm låsesystem og dørramme. DNМК dørtilbehørssæt (hængsler, låsebeslag) skal bestilles separat. Alt ekstraudstyr i låseprogrammet samt 180° hængsler kan benyttes. Kompatibelt med kombinerbare og kompakte skabsserier.

Materiale: 2 mm stålplade.

Maksimal belastning: 800 N.

Overfladebehandling: RAL 7035 struktur pulvermaling.

Monteringskrav: Anvend hængsel sæt DNМК hvis dør ikke tidligere har været monteret.

Pakke størrelse: 1 stk.

## SPECIFIKATIONER

**Farve:** Light Gray  
**Materiale:** Lakeret Stål  
**Finish:** Struktur Pulvermaling  
**Farvekode:** RAL 7035

Table 1/3

Katalognummer	Højde	Bredde	Dybde	Door Type	Enclosure Material	Produktfamilie
DN1804R5	1782mm	393mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2208R5	2182mm	793mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1606RR5	1582mm	593mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1208R5	1182mm	793mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1805RR5	1782mm	493mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1810R5	1782mm	993mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1804LR5	1782mm	393mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1406RR5	1382mm	793mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1808LR5	1782mm	793mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN2008RR5	1982mm	793mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1806R5	1782mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2206LR5	2182mm	593mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1206RR5	1182mm	593mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1606R5	1582mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1408R5	1382mm	793mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2004LR5	1982mm	393mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1206R5	1182mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2006R5	1982mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1808R5	1782mm	793mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1406LR5	1382mm	593mm	17mm	Left Door	Lakeret Stål	Free-Standing

Table 2/3

Katalognummer	Højde	Bredde	Dybde	Door Type	Enclosure Material	Produktfamilie
DN2005RR5	1982mm	493mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1608R5	1582mm	793mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2206R5	2182mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2010R5	1982mm	993mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2206RR5	2182mm	593mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1806LR5	1782mm	593mm	17mm	Left Door	Lakeret Stål	Free-Standing

Katalognummer	Højde	Bredde	Dybde	Door Type	Enclosure Material	Produktfamilie
DN2205LR5	2182mm	493mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1405RR5	1382mm	493mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1406R5	1382mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1808RR5	1782mm	793mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1610R5	1582mm	993mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2006RR5	1982mm	593mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1405LR5	1382mm	493mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN2005R5	1982mm	493mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1606LR5	1582mm	593mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1805LR5	1782mm	493mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1206LR5	1182mm	593mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1805R5	1782mm	493mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2004RR5	1982mm	393mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN2005LR5	1982mm	493mm	17mm	Left Door	Lakeret Stål	Free-Standing

Table 3/3

Katalognummer	Højde	Bredde	Dybde	Door Type	Enclosure Material	Produktfamilie
DN2008R5	1982mm	793mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2210R5	2182mm	993mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2004R5	1982mm	393mm	17mm	Plain	Lakeret Stål	Free-Standing
DN1806RR5	1782mm	593mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN2205RR5	2182mm	493mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN2006LR5	1982mm	593mm	17mm	Left Door	Lakeret Stål	Free-Standing
DN1804RR5	1782mm	393mm	17mm	Right Door	Lakeret Stål	Free-Standing
DN1106R5	1082mm	593mm	17mm	Plain	Lakeret Stål	Free-Standing
DN2008LR5	1982mm	793mm	17mm	Left Door	Lakeret Stål	Free-Standing

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**