


Comptec GND/Earthing Kit



Protective GND/earthing connections in accordance with:
DIN EN 50178, VDE 0160 DIN EN 62368-1, VDE 0805 DIN EN
61010-1, VDE 0411 Part 1 DIN EN 61010-1A2, VDE 0411
Part 1/A1.

CERTIFICERINGER



FUNKTIONER

Protective GND/earthing connections in accordance with: DIN EN 50178/VDE 0160 DIN EN 62368-1/VDE 0805
DIN EN 61010-1 /VDE 0411 Part 1 DIN EN 61010-1A2 /VDE 0411 Part 1/A1

VDE tested

SPECIFIKATIONER

Produktfamilie: Comptec
Type: Grounding Kit
Product Type: Grounding Kit

Table 1/1

Katalognummer	Pakke mængde	Works With
21100-490	1	Cases, Steel Cover
21100-448	1	Cases, Steel Cover
21100-347	1	Cases, Aluminum Cover

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE