

MTCA.4 System Rev3, 12 Double Mid-Size AMC Slots, 9 U, 84 HP, JSM

KATALOGNUMMER

11850-040



MTCA.4 crate in accordance to Rev 3.0 of the MTCA.0 Standard with support for PCIe Gen 4 & 5 as well as 100 GbE. The system is designed for high-performance applications with high level of availability, where redundancy of all components is required. The two redundant hot-swap fan modules with EMMC in push-pull configuration ensure that the front and rear slots are properly cooled. The fan speed is controlled independently for front and rear and is set via the MCH. Cable trays on the front and rear of the enclosure simplify cable management. The system can take up to four power modules to ensure a sufficient power supply for the application. The backplane features clock and trigger lines per PICMG MTCA.4, as well as interlocks. It also provides direct connections for SAS/SATA and lines between the AMCs.

FUNKTIONER

In accordance with PICMG MTCA.0 R3.0 and MTCA.4 R3.0 specification

Supports PCIe Gen5 and 100GBase-KR4

9 U, 84 HP system for 12 Double Mid-Size AdvancedMC modules, 2 Double Full-Size MCHs, and 4 Double Full-Size power modules

12 rear transition module slots for Double Mid-Size RTMs

Backplane with dual star topology, direct connections for S-ATA / SAS, clock and trigger lines per PICMG MTCA.4

Telecom and fabric clock topology per PICMG AMC.0 R2.0

2 hot-swap fan modules with cooling unit manager (CU EMMC), airflow from bottom front to top rear

Fan tray suitable for chassis with 80 W CU Power Channel (MTCA.0 R2.0) or 110 W CU Power Channel (MTCA.0 R3.0)

Optionally fan speeds for front and rear sections can be separately adjusted via the MCH

PRODUKTEGENSKABER

Product Type: System

Number of Slots: 12

Type: 19" Rack Mount

Backplane Type: MTCA.4 Star Topology

Data Transfer: 100 GbE; PCIe Gen5

Power per Slot: 80W

Airflow Direction: Front to Rear

Rack Height: 9U

Power Supply Type: (4) Double Full-size PM

Power Supply Included: No

Rear I/O: Yes

Complies With: PICMG MTCA.4 R1.0

Dybde: 373.3mm

Højde: 400.05mm

YDERLIGERE PRODUKTOPLYSNINGER

Modified systems available on request.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE