

PSU 19" AC/DC for CompactPCI Serial, 3 U, 8 HP, 312 W

KATALOGNUMMER

13100-147



Pluggable 19" Power Supply, for CompactPCI applications. The Power Supply has a wide range AC input, a 12V DC Payload and +5 V DC Standby output.

FUNKTIONER

19" pluggable PSU for CompactPCI Serial applications

Active power factor correction and active current-share function

N+1 redundancy, hot swap

Output signaling: PS present, power failure, PS_ON and enable

I2C interface

High efficiency, > 90% at 220 VAC

PRODUKTEGENSKABER

Product Type: Power Supply

Type: 19" Switched-Mode

Works With: CompactPCI Systems

Indgangsspænding AC: 90 – 264V

Power: 312W

Number of Output Voltages: 2

Voltage 1: 12V

Current 1: 25A

Voltage 2: 5V

Current 2: 2.5A

Rack Height: 3U

Gross Weight: 0.948kg

Pakke mængde: 1

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE