

AC Fan, 230 VAC, 119 x 119 x 25 mm, 108 m³h

KATALOGNUMMER

20700-001

Axial fan, 119 mm, with AC input. Replacement part for 1 U fan trays.



CERTIFICERINGER



FUNKTIONER

119 mm DC fan with plug for connection cable

PRODUKTEGENSKABER

Product Type: Fan

Works With: 19" Fan Trays

Bredde: 119mm

Length: 119mm

Højde: 25mm

Spænding AC: 230V

Frequency: 50/60 Hz

Airflow @ 50 Hz: 108m³/h

Airflow @ 60 Hz: 120m³/h

Noise Level @ 50 Hz: 34dB(A)

Noise Level @ 60 Hz: 38dB(A)

Power @ 50 Hz: 14W

Power @ 60 Hz: 11W

Max Static Pressure: 41Pa

Omgivelsestemperatur: 70°C

Gross Weight: 0.338kg

Pakke mængde: 1

YDERLIGERE PRODUKTOPLYSNINGER

Please order connection cable and protective grille separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelser af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE