


Insertor/Extractor Handle Type IET, Grey Lever, Black Button, Bottom, 10 Piece

KATALOGNUMMER

20817-714



The inserter/extractor handle, type IET in accordance with IEEE 1101.10, 0,1" offset. Two of these handles can overcome a single lever force of 700 N (per pair).

CERTIFICERINGER



FUNKTIONER

Suitable for insertion and extraction forces up to 700 N (per pair)

In accordance with IEEE 1101.10 and IEC 60297-3-102

A microswitch can be mounted

0.1" offset is used for PSUs with SMD Plus

PRODUKTEGENSKABER

Pakke mængde: 10

Håndtagstype: IET; Bottom Front

Flammability Rating: UL® 94V-0

Farve: Grey

Complies With: EN 45545-2

Materiale: Polycarbonate

Product Type: Handle


Type: Inserter/Extractor, 0.1" Offset

Works With: Front Panels

YDERLIGERE PRODUKTOPLYSNINGER

Please order Coding pegs and Microswitch separately.

DIAGRAMS



ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer.

Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug,

fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE