

EuropacPRO Cover Plate for Horizontal Rail Type L, Light, 84 HP, 175 mm

KATALOGNUMMER

24561-051



Mechanical covering of installed components. The plate is inserted into a groove of the L type horizontal rails.

CERTIFICERINGER



FUNKTIONER

Mechanical covering of installed components

Suitable for "light" and "flexible" sub racks, for insertion into the groove of the light (type L) horizontal rails

Perforation ratio approx. 60%

PRODUKTEGENSKABER

Rack Width: 84HP

Dybde: 175mm

Pakke mængde: 2

Materiale: Aluminium

Produktfamilie: EuropacPRO

Product Type: Cover Plate

Type: Perforated

Works With: Subracks

Net Weight: 0.15kg

Pakkeenhed: Pair

YDERLIGERE PRODUKTOPLYSNINGER

Other dimensions on request.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE