


EuropacPRO Advanced EMC Side Panel Cover, 4U, 295 mm

KATALOGNUMMER

24563-267



Aluminium Side panel 3mm to increase the EMC shielding effect of the subrack by covering the not needed cut-outs.

CERTIFICERINGER



FUNKTIONER

Side panel covers for increased lateral RF shielding

Assembled on the outside of the standard side panel

Assembly material included

PRODUKTEGENSKABER

Rack Height: 4U

Dybde: 295mm

Pakke mængde: 2

EMC Shielding: Yes

Finish: Passivated

Length: 295mm

Materiale: Aluminium

Produktfamilie: EuropacPRO

Product Type: Side Panel

Type: Type H

Works With: Subracks

Pakkeenhed: Pair

YDERLIGERE PRODUKTOPLYSNINGER

Side panel and 19" bracket are tox-cold welded together. toxen = Clinching technique, without add aids. This takes place with special tools and high pressure.

9 U version available on request.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE