


# Horizontal Rail, Rear, Type R-ST, Rugged, Standard, 63 HP

## KATALOGNUMMER

**34566-563**



Combinations of horizontal rails and side panels

|                 |             | "R" can be combined |   | "ST" combination not recommended |   |
|-----------------|-------------|---------------------|---|----------------------------------|---|
| Horizontal rail | Rugged + R  | -                   | + | +                                | + |
|                 | Rugged + ST | +                   | + | +                                | + |
| Horizontal rail | Rugged + R  | +                   | + | +                                | + |
|                 | Rugged + ST | +                   | + | +                                | + |
| Horizontal rail | Rugged + R  | +                   | + | +                                | + |
|                 | Rugged + ST | +                   | + | +                                | + |
| Horizontal rail | Rugged + R  | +                   | + | +                                | + |
|                 | Rugged + ST | +                   | + | +                                | + |

Side panel

Light + R, Rugged + R, Heavy + R, Rugged + ST

The horizontal rail, type rugged ST enable the isolated assembly of a backplane. The isolation is done by an insulation strip.

## CERTIFICERINGER



## FUNKTIONER

Type R-ST "rugged" horizontal rail with 3-hole fixing for increased robustness

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

With HP units printed from 28 HP upwards

## PRODUKTEGENSKABER

Rack Width: 63HP

Pakke mængde: 1

Finish: Anodized

Length: 325.12mm

Materiale: Aluminium

Produktfamilie: EuropacPRO

Product Type: Horizontal Rail

Type: Rugged, ST

Works With: Subracks

Net Weight: 0.167kg

## YDERLIGERE PRODUKTOPLYSNINGER

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**