

Inpac 19" Chassis



The nVent SCHROFF Inpac chassis, provides electronics protection for 19" and individual electronic assemblies and also can be used for desktop applications.

CERTIFICERINGER



FUNKTIONER

Grounding/earthing kit optional

RAL 7030 powder coat finish

For assembly with 19" components or individually with mounting plates

Three rows of ventilation slots in base for air inlet

Aluminum construction with die-cast front and rear frames

IP 20, in accordance with IEC 60529

External dimensions in accordance with IEC 60297-3-101

Grounding/earthing connectors to: DIN EN 50178/VDE 0160, DIN EN 62368-1/VDE 0805, DIN EN 61010-1/VDE 0411 part 1, DIN EN 61010-1A2/VDE 0411 part 1/A1

Modifications such as cutouts or paint available

SPECIFIKATIONER

Rack Width: 84HP

Product Type: Case

Produktfamilie: Inpac

Table 1/2

Katalognummer	Rack Height	Dybde	Pakke mængde	Mounting	Complies With	EMC Shielding
10828-156	4U	254.5mm	1	Rack	IEC 60297-3-101	No
10828-171	2U	254.5mm	1	Rack	IEC 60297-3-101	No
10828-169	6U	434.5mm	1	Rack	IEC 60297-3-101	No
10828-152	3U	314.5mm	1	Rack	IEC 60297-3-101	No
10828-153	3U	374.5mm	1	Rack	IEC 60297-3-101	No
10828-168	6U	374.5mm	1	Rack	IEC 60297-3-101	No
10828-159	4U	434.5mm	1	Rack	IEC 60297-3-101	No
10828-172	2U	314.5mm	1	Rack	IEC 60297-3-101	No
10828-154	3U	434.5mm	1	Rack	IEC 60297-3-101	No
10828-173	2U	374.5mm	1	Rack	IEC 60297-3-101	No
10828-158	4U	374.5mm	1	Rack	IEC 60297-3-101	No
10828-157	4U	314.5mm	1	Rack	IEC 60297-3-101	No
10828-151	3U	254.5mm	1	Rack	IEC 60297-3-101	No

Table 2/2

Katalognummer	Finish	Materiale	Static Load
10828-156	Struktur Pulvermaling	Aluminium, Stål	15kg
10828-171	Struktur Pulvermaling	Aluminium, Stål	15kg
10828-169	Struktur Pulvermaling	Aluminium, Stål	15kg
10828-152	Struktur Pulvermaling	Aluminium, Stål	15kg
10828-153	Struktur Pulvermaling	Aluminium, Stål	15kg
10828-168	Struktur Pulvermaling	Aluminium, Stål	15kg
10828-159	Struktur Pulvermaling	Aluminium, Stål	15kg
10828-172	Struktur Pulvermaling	Aluminium, Stål	15kg
10828-154	Struktur Pulvermaling	Aluminium, Stål	15kg

Katalognummer	Finish	Materiale	Static Load
10828-173	Struktur Pulvermaling	Aluminium, Stål	15kg
10828-158	Struktur Pulvermaling	Aluminium, Stål	15kg
10828-157	Struktur Pulvermaling	Aluminium, Stål	15kg
10828-151	Struktur Pulvermaling	Aluminium, Stål	15kg

YDERLIGERE PRODUKTOPLYSNINGER

Max. installation space when fitting 19" components is 75 HP.

Scope of delivery includes screws to fix rear and front panels.

Cover and base plate available in other colors.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE