

Interscale 19" Rack Mount Chassis, Perforated

Flexible 19" Chassis with integrated EMC protection and perforated side. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.



CERTIFICERINGER



FUNKTIONER

Modular desktop case consisting of 4 assembled parts, with perforated sides

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 20

Color RAL 7016

Modified or customized cases upon request

SPECIFIKATIONER

Materiale:	Stål; Aluminium
Produktfamilie:	Interscale
Type:	Perforated
Product Type:	Small Form Factor Case
EMC Shielding:	Yes

Table 1/2

Katalognummer	Rack Height	Dybde	Pakke mængde	Usable Width	Mounting	Complies With
---------------	-------------	-------	--------------	--------------	----------	---------------

14826-105	1U	221mm	1	444mm	Rack	IEC 60297-3-100
14826-107	1U	310mm	1	444mm	Rack	IEC 60297-3-100
14826-307	3U	310mm	1	444mm	Rack	IEC 60297-3-100
14826-305	3U	221mm	1	444mm	Rack	IEC 60297-3-100
14826-207	2U	310mm	1	444mm	Rack	IEC 60297-3-100
14826-205	2U	221mm	1	444mm	Rack	IEC 60297-3-100

Table 2/2

Katalognummer	Finish
14826-105	Aluminum-Zinc Plated, Struktur Pulvermaling
14826-107	Aluminum-Zinc Plated, Struktur Pulvermaling
14826-307	Aluminum-Zinc Plated, Struktur Pulvermaling
14826-305	Aluminum-Zinc Plated, Struktur Pulvermaling
14826-207	Aluminum-Zinc Plated, Struktur Pulvermaling
14826-205	Aluminum-Zinc Plated, Struktur Pulvermaling

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE