

Interscale Desktop Case, Perforated



Flexible desktop case with integrated EMC protection and perforated sides. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.

CERTIFICERINGER



FUNKTIONER

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 20

Color RAL 7016

Modified or customized cases upon request

SPECIFIKATIONER

| | |
|--------------------------|------------------------|
| Materiale: | Aluminium; Stål |
| Type: | Desktop |
| Produktfamilie: | Interscale |
| Beskyttelsesgrad: | IP20 |
| Farvekode: | RAL 7016 |
| Product Type: | Small Form Factor Case |

Table 1/2

| Katalognummer | Højde | Pakke mængde | Bredde | Dybde | Cooling | Farve |
|---------------|---------|--------------|--------|-------|------------|-----------------|
| 14825-154 | 43.7mm | 1 | 221mm | 177mm | Perforated | Anthracite Grey |
| 14825-254 | 88.1mm | 1 | 221mm | 177mm | Perforated | Anthracite Grey |
| 14825-255 | 88.1mm | 1 | 221mm | 221mm | Perforated | Anthracite Grey |
| 14825-197 | 43.7mm | 1 | 399mm | 310mm | Perforated | Anthracite Grey |
| 14825-275 | 88.1mm | 1 | 310mm | 221mm | Perforated | Anthracite Grey |
| 14825-195 | 43.7mm | 1 | 399mm | 221mm | Perforated | Anthracite Grey |
| 14825-295 | 88.1mm | 1 | 399mm | 221mm | Perforated | Anthracite Grey |
| 14825-297 | 88.1mm | 1 | 399mm | 310mm | Perforated | Anthracite Grey |
| 14825-175 | 43.7mm | 1 | 310mm | 221mm | Perforated | Anthracite Grey |
| 14825-375 | 132.6mm | 1 | 310mm | 221mm | Perforated | Anthracite Grey |
| 14825-395 | 132.6mm | 1 | 399mm | 221mm | Perforated | Anthracite Grey |
| 14825-155 | 43.7mm | 1 | 221mm | 221mm | Perforated | Anthracite Grey |
| 14825-397 | 132.6mm | 1 | 399mm | 310mm | Perforated | Anthracite Grey |

Table 2/2

| Katalognummer | Finish |
|---------------|---|
| 14825-154 | Aluminum-Zinc Plated, Struktur Pulvermaling |
| 14825-254 | Aluminum-Zinc Plated, Struktur Pulvermaling |
| 14825-255 | Aluminum-Zinc Plated, Struktur Pulvermaling |
| 14825-197 | Aluminum-Zinc Plated, Struktur Pulvermaling |
| 14825-275 | Aluminum-Zinc Plated, Struktur Pulvermaling |
| 14825-195 | Aluminum-Zinc Plated, Struktur Pulvermaling |
| 14825-295 | Aluminum-Zinc Plated, Struktur Pulvermaling |
| 14825-297 | Aluminum-Zinc Plated, Struktur Pulvermaling |
| 14825-175 | Aluminum-Zinc Plated, Struktur Pulvermaling |
| 14825-375 | Aluminum-Zinc Plated, Struktur Pulvermaling |
| 14825-395 | Aluminum-Zinc Plated, Struktur Pulvermaling |
| 14825-155 | Aluminum-Zinc Plated, Struktur Pulvermaling |
| 14825-397 | Aluminum-Zinc Plated, Struktur Pulvermaling |

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE