

Outdoor Comline ECL Cabinet



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism ensuring operational continuity.

CERTIFICERINGER



FUNKTIONER

IP 55

Heat dissipation through natural convection

Single wall, lightweight aluminium cabinet

SPECIFIKATIONER

Materiale: Aluminium

Table 1/3

Katalognummer	Product Type	Produktfamilie	Rack Height	Højde	Bredde	Dybde
12349-003	Outdoor Cabinet	Comline ECL	18U	900mm	700mm	600mm
12349-001	Outdoor Cabinet	Comline ECL	12U	600mm	600mm	500mm
12349-010	Outdoor Cabinet	Comline ECL	18U	900mm	600mm	500mm

Katalognummer	Product Type	Produktfamilie	Rack Height	Højde	Bredde	Dybde
12349-011	Outdoor Cabinet	Comline ECL	18U	900mm	700mm	600mm
12349-009	Outdoor Cabinet	Comline ECL	12U	600mm	600mm	500mm
12349-004	Outdoor Cabinet	Comline ECL	25U	1200mm	700mm	600mm
12349-012	Outdoor Cabinet	Comline ECL	25U	1200mm	700mm	600mm
12349-002	Outdoor Cabinet	Comline ECL	18U	900mm	600mm	500mm

Table 2/3

Katalognummer	Wall Type	Door Type	Access	Cooling	EMC Shielding	Complies With
12349-003	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-001	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-010	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-011	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

Katalognummer	Wall Type	Door Type	Access	Cooling	EMC Shielding	Complies With
12349-009	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-004	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-012	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-002	Single Walled	Single Door	Front	Natural Convection	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

Table 3/3

Katalognummer	Pakke mængde	Finish
12349-003	1	Struktur Pulvermaling
12349-001	1	Struktur Pulvermaling
12349-010	1	Struktur Pulvermaling
12349-011	1	Struktur Pulvermaling
12349-009	1	Struktur Pulvermaling
12349-004	1	Struktur Pulvermaling
12349-012	1	Struktur Pulvermaling
12349-002	1	Struktur Pulvermaling

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE