

PCB Solder Side Cover

A solder side cover protects the solder side of a PCB mechanically.



CERTIFICERINGER



FUNKTIONER

Mechanical protection of solder side

Suitable for 100 x 160 mm Euroboard

SPECIFIKATIONER

- Product Type:** Cover
- Works With:** Front Panels
- Materiale:** Polypropylene
- Type:** Solder Side Cover

Table 1/1

Katalognummer	Rack Height	Pakke mængde	Temperature	Flammability Rating
61000-007	3U	1	55°C min	UL@ 94V-0
61000-177	3U	1	85°C min	UL@ 94V-0
61000-012	6U	1	55°C min	UL@ 94V-0

YDERLIGERE PRODUKTOPLYSNINGER

The materials of the PCB cover are UL-listed. The test was conducted with material thickness 1.5 mm.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE