

# PropacPRO Complete Desktop Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

## CERTIFICERINGER



## FUNKTIONER

Desktop case, pre-configured in accordance with IEC 60297-3-101 for 19" components

Unshielded

Ventilation slots in base plate

Rear panel perforated

Conforms with DIN EN 62368-1

## SPECIFIKATIONER

<b>Static Load:</b>	25kg
<b>Product Type:</b>	Case
<b>Type:</b>	Case for 19" Components
<b>EMC Shielding:</b>	No (Retrofittable)
<b>Produktfamilie:</b>	PropacPRO

Table 1/3

Katalognummer	Rack Height	Rack Width	Dybde	Pakke mængde	Usable Height	Usable Width
24576-022	6U	84HP	446mm	1	245.7mm	432mm
24576-005	3U	42HP	386mm	1	112.3mm	219mm
24576-002	3U	28HP	326mm	1	112.3mm	148mm
24576-010	3U	84HP	326mm	1	112.3mm	432mm
24576-011	3U	84HP	386mm	1	112.3mm	432mm
24576-021	6U	84HP	326mm	1	245.7mm	432mm
24576-004	3U	42HP	326mm	1	112.3mm	219mm
24576-006	3U	63HP	266mm	1	112.3mm	326mm
24576-009	3U	84HP	266mm	1	112.3mm	432mm
24576-012	3U	84HP	446mm	1	112.3mm	432mm
24576-013	3U	84HP	506mm	1	112.3mm	432mm
24576-003	3U	42HP	266mm	1	112.3mm	219mm
24576-007	3U	63HP	326mm	1	112.3mm	326mm
24576-001	3U	28HP	266mm	1	112.3mm	148mm
24576-008	3U	63HP	386mm	1	112.3mm	326mm

Table 2/3

Katalognummer	Front Frame Construction	Cooling Option	Complies With	Finish	Højde	Materiale
24576-022	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	289mm	Aluminium
24576-005	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-002	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-010	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-011	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-021	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	289mm	Aluminium

Katalognummer	Front Frame Construction	Cooling Option	Complies With	Finish	Højde	Materiale
24576-004	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-006	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-009	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-012	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-013	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-003	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-007	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-001	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium
24576-008	Single Piece	No	IEC 60297-3-101	Passivated, Struktur Pulvermaling	155.5mm	Aluminium

Table 3/3

Katalognummer	Beskyttelsesgrad	Bredde
24576-022	IP20	470.3mm
24576-005	IP20	257mm
24576-002	IP20	185.9mm
24576-010	IP20	470.3mm
24576-011	IP20	470.3mm
24576-021	IP20	470.3mm
24576-004	IP20	257mm
24576-006	IP20	363.7mm
24576-009	IP20	470.3mm
24576-012	IP20	470.3mm
24576-013	IP20	470.3mm

Katalognummer	Beskyttelsesgrad	Bredde
24576-003	IP20	257mm
24576-007	IP20	363.7mm
24576-001	IP20	185.9mm
24576-008	IP20	363.7mm

## ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på [www.nvent.com](http://www.nvent.com) og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unkladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Vores kraftfulde portefølje af mærker:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**