

PropacPRO Portable Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" and individual electronic assemblies. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition this case is prepared for the fitting of a tip-up carrying handle, which is part of the extensive accessory range.

CERTIFICERINGER



FUNKTIONER

Desktop case for individual assembly

Prepared with holes for fitting of tip-up carrying handle

Retrofitable EMC shielding

Ventilation slots in base plate

IP 20 in accordance with IEC 60529

Prepared for GND/earthing

Conforms with DIN EN 62368-1

SPECIFIKATIONER

- Product Type:** Case
- Type:** Case for Individual Electronic Components
- Produktfamilie:** PropacPRO

Table 1/3

Katalognummer	Rack Height	Rack Width	Dybde	Pakke mængde	Usable Height	Usable Width
14577-163	3U	84HP	326mm	1	130mm	432mm

Katalognummer	Rack Height	Rack Width	Dybde	Pakke mængde	Usable Height	Usable Width
14577-125	3U	42HP	386mm	1	130mm	219mm
14577-123	3U	42HP	326mm	1	130mm	219mm
14577-265	4U	84HP	386mm	1	174mm	432mm
14577-143	3U	63HP	326mm	1	130mm	326mm
14577-245	4U	63HP	386mm	1	174mm	326mm
14577-165	3U	84HP	386mm	1	130mm	432mm
14577-243	4U	63HP	326mm	1	174mm	326mm
14577-145	3U	63HP	386mm	1	130mm	326mm
14577-223	4U	42HP	326mm	1	174mm	219mm

Table 2/3

Katalognummer	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Finish	Højde
14577-163	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14577-125	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14577-123	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14577-265	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm
14577-143	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14577-245	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm
14577-165	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm
14577-243	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm
14577-145	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	155.5mm

Katalognummer	Front Frame Construction	Cooling Option	Complies With	EMC Shielding	Finish	Højde
14577-223	Single Piece	No	IEC 60297-3-101	No (Retrofittable)	Passivated, Struktur Pulvermaling	200mm

Table 3/3

Katalognummer	Materiale	Beskyttelsesgrad	Static Load	Bredde
14577-163	Aluminium	IP20	25kg	470.3mm
14577-125	Aluminium	IP20	25kg	257mm
14577-123	Aluminium	IP20	25kg	257mm
14577-265	Aluminium	IP20	25kg	470.3mm
14577-143	Aluminium	IP20	25kg	363.7mm
14577-245	Aluminium	IP20	25kg	363.7mm
14577-165	Aluminium	IP20	25kg	470.3mm
14577-243	Aluminium	IP20	25kg	363.7mm
14577-145	Aluminium	IP20	25kg	363.7mm
14577-223	Aluminium	IP20	25kg	257mm

YDERLIGERE PRODUKTOPLYSNINGER

Please order tip up carrying handle separatly.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE