

PSU 19" AC/DC Linear Regulator, Single

Linear regulator for applications requiring very low output noise level.



CERTIFICERINGER



FUNKTIONER

1 output voltage

High control accuracy, low residual ripple and low interference

Mains/line voltage 230 VAC (can be switched to 115 VAC with mains/line voltage conversion kit)

Suited for medical applications (8 mm safety clearances)

SPECIFIKATIONER

Table 1/2

Katalognummer	Type	Indgangsspænding AC	Power	Number of Output Voltages	Voltage 1	Current 1
13105-004	19" Linear Regulator	230V	16W	1	24V	0.6A
13105-003	19" Linear Regulator	230V	15W	1	15V	1A
13105-009	19" Linear Regulator	230V	36W	1	24V	1.5A

Katalognummer	Type	Indgangsspænding AC	Power	Number of Output Voltages	Voltage 1	Current 1
13105-001	19" Linear Regulator	230V	8W	1	5V	1.5A
13105-011	19" Linear Regulator	230V	30W	1	5V	6A
13105-008	19" Linear Regulator	230V	33W	1	15V	2.2A
13105-007	19" Linear Regulator	230V	31W	1	12V	2.8A
13105-012	19" Linear Regulator	230V	50W	1	12V	4.2A
13105-014	19" Linear Regulator	230V	60W	1	24V	2.5A
13105-006	19" Linear Regulator	230V	20W	1	5V	4A
13105-002	19" Linear Regulator	230V	13W	1	12V	1.1A
13105-013	19" Linear Regulator	230V	53W	1	15V	3.5A

Table 2/2

Katalognummer	Rack Height	Rack Width	Dybde	Pakke mængde	Certificeringer
13105-004	3U	6HP	171.93mm	1	RoHS, CE, EN 62368-1
13105-003	3U	6HP	171.93mm	1	CE, EN 62368-1, RoHS
13105-009	3U	10HP	171.93mm	1	CE, RoHS
13105-001	3U	6HP	171.93mm	1	EN 62368-1, CE, RoHS
13105-011	3U	14HP	171.93mm	1	CE, RoHS
13105-008	3U	10HP	171.93mm	1	CE, RoHS
13105-007	3U	10HP	171.93mm	1	CE, RoHS
13105-012	3U	14HP	171.93mm	1	CE, RoHS
13105-014	3U	14HP	171.93mm	1	RoHS, CE
13105-006	3U	10HP	171.93mm	1	CE, RoHS
13105-002	3U	6HP	171.93mm	1	CE, EN 62368-1, RoHS
13105-013	3U	14HP	171.93mm	1	RoHS, CE

YDERLIGERE PRODUKTOPLYSNINGER

Please order Front Panel separately.

Output Data at Ta= 0 ... 50 °C.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelser af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE