

Socket Strip, UTE



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with UTE outlets.

CERTIFICERINGER



FUNKTIONER

230 V, 16 A

In accordance with NFC 61-303

Socket strip with UTE sockets

Mounting height 1 U

Horizontal or vertical mounting

Connecting cable 2 m, with SCHUKO/UTE plug

Socket strips can be rotated through all four directions (in 90° increments) during installation

SPECIFIKATIONER

Materiale: Aluminium; Polyamide

Farve: Grey

Product Type: Socket Strip

Table 1/2

Katalognummer	Stiktype	Socket Quantity	Switched Outlets	Spænding AC	Function	Pakke mængde
60110-226	UTE	12	Yes	230V		1

Katalognummer	Stiktype	SocketQuantity	Switched Outlets	Spænding AC	Function	Pakke mængde
60110-222	UTE	12	No	230V		1
60110-221	UTE	9	No	230V		1
60110-267	UTE	6	No	230V	Transient Protection, Mains Suppression Filter	1
60110-223	UTE	15	No	230V		1
60110-224	UTE	19	No	230V		1
60110-225	UTE	8	Yes	230V		1
60110-231	UTE	6	No	230V	Fault Current Protection, Overcurrent Protection	1
60110-227	UTE	8	No	230V	Transient Protection	1
60110-228	UTE	6	No	230V	Overcurrent Protection	1
60110-220	UTE	4	No	230V		1
60110-230	UTE	6	No	230V	Fault Current Protection	1
60110-229	UTE	7	No	230V	Mains Suppression Filter	1

Table 2/2

Katalognummer	Dybde	Finish	Length
60110-226	44mm	Anodized	947.5mm
60110-222	44mm	Anodized	947.5mm
60110-221	44mm	Anodized	438.5mm
60110-267	44mm	Anodized	438.5mm
60110-223	44mm	Anodized	1202mm
60110-224	44mm	Anodized	1753mm
60110-225	44mm	Anodized	438.5mm
60110-231	88mm	Anodized	438.5mm
60110-227	44mm	Anodized	438.5mm
60110-228	75mm	Anodized	438.5mm
60110-220	44mm	Anodized	210mm
60110-230	88mm	Anodized	438.5mm

Katalognummer	Dybde	Finish	Length
60110-229	44mm	Anodized	438.5mm

YDERLIGERE PRODUKTOPLYSNINGER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE