


Varistar CP Frame



Varistar CP welded frame is available for static load requirements and can be integrated with 19", ETSI or mounting plate. Additionally, castors can be added to the frame if needed.

However, if you require castors for your application, you might want to consider a mobile frame that already includes castors.

FUNKTIONER

Welded, finish powder-coated, black gray, RAL 7021

St, 1.5 mm, zinc-plated, with central GND/grounding point

Static load-carrying capacity max. 1600 kg

Please order adjustable feet separately

SPECIFIKATIONER

Static Load: 1600kg
Product Type: Cabinet/Rack Frame
Materiale: Stål

Table 1/2

Katalognummer	Rack Height	Højde	Bredde	Dybde	Pakke mængde	Farve
20630-118	47U	2200mm	800mm	800mm	1	Black Grey
20630-067	24U	1200mm	600mm	900mm	1	Black Grey
20630-091	38U	1800mm	600mm	600mm	1	Black Grey
20630-120	47U	2200mm	800mm	1000mm	1	Black Grey
20630-084	33U	1600mm	600mm	800mm	1	Black Grey
20630-126	52U	2450mm	800mm	1000mm	1	Black Grey
20630-092	38U	1800mm	600mm	800mm	1	Black Grey
20630-119	47U	2200mm	800mm	900mm	1	Black Grey
20630-125	52U	2450mm	600mm	1200mm	1	Black Grey

Katalognummer	Rack Height	Højde	Bredde	Dybde	Pakke mængde	Farve
20630-075	29U	1400mm	600mm	600mm	1	Black Grey
20630-089	33U	1600mm	800mm	900mm	1	Black Grey
20630-072	24U	1200mm	800mm	800mm	1	Black Grey
20630-117	47U	2200mm	800mm	600mm	1	Black Grey
20630-095	38U	1800mm	800mm	600mm	1	Black Grey
20630-128	52U	2450mm	800mm	1200mm	1	Black Grey
20630-114	47U	2200mm	600mm	1000mm	1	Black Grey
20630-096	38U	1800mm	800mm	800mm	1	Black Grey
20630-124	52U	2450mm	600mm	1100mm	1	Black Grey
20630-079	29U	1400mm	800mm	600mm	1	Black Grey
20630-093	38U	1800mm	600mm	900mm	1	Black Grey
20630-087	33U	1600mm	800mm	600mm	1	Black Grey
20630-074	24U	1200mm	800mm	1000mm	1	Black Grey
20630-094	38U	1800mm	600mm	1000mm	1	Black Grey
20630-077	29U	1400mm	600mm	900mm	1	Black Grey
20630-073	24U	1200mm	800mm	900mm	1	Black Grey
20630-076	29U	1400mm	600mm	800mm	1	Black Grey
20630-122	47U	2200mm	800mm	1200mm	1	Black Grey
20630-101	42U	2000mm	600mm	900mm	1	Black Grey
20630-097	38U	1800mm	800mm	900mm	1	Black Grey
20630-090	33U	1600mm	800mm	1000mm	1	Black Grey
20630-088	33U	1600mm	800mm	800mm	1	Black Grey
20630-098	38U	1800mm	800mm	1000mm	1	Black Grey
20630-068	24U	1200mm	600mm	1000mm	1	Black Grey
20630-078	29U	1400mm	600mm	1000mm	1	Black Grey
20630-123	52U	2450mm	600mm	1000mm	1	Black Grey
20630-112	47U	2200mm	600mm	800mm	1	Black Grey
20630-102	42U	2000mm	600mm	1000mm	1	Black Grey
20630-085	33U	1600mm	600mm	900mm	1	Black Grey
20630-065	24U	1200mm	600mm	600mm	1	Black Grey
20630-110	42U	2000mm	800mm	1200mm	1	Black Grey
20630-083	33U	1600mm	600mm	600mm	1	Black Grey
20630-105	42U	2000mm	800mm	600mm	1	Black Grey
20630-109	42U	2000mm	800mm	1100mm	1	Black Grey

Katalognummer	Rack Height	Højde	Bredde	Dybde	Pakke mængde	Farve
20630-082	29U	1400mm	800mm	1000mm	1	Black Grey
20630-106	42U	2000mm	800mm	800mm	1	Black Grey
20630-100	42U	2000mm	600mm	800mm	1	Black Grey
20630-086	33U	1600mm	600mm	1000mm	1	Black Grey
20630-107	42U	2000mm	800mm	900mm	1	Black Grey
20630-066	24U	1200mm	600mm	800mm	1	Black Grey
20630-104	42U	2000mm	600mm	1200mm	1	Black Grey
20630-080	29U	1400mm	800mm	800mm	1	Black Grey
20630-108	42U	2000mm	800mm	1000mm	1	Black Grey
20630-081	29U	1400mm	800mm	900mm	1	Black Grey
20630-127	52U	2450mm	800mm	1100mm	1	Black Grey
20630-071	24U	1200mm	800mm	600mm	1	Black Grey
20630-261	42U	2000mm	600mm	300mm	1	Black Grey
20630-111	47U	2200mm	600mm	600mm	1	Black Grey
20630-115	47U	2200mm	600mm	1100mm	1	Black Grey
20630-113	47U	2200mm	600mm	900mm	1	Black Grey
20630-121	47U	2200mm	800mm	1100mm	1	Black Grey
20630-262	47U	2200mm	600mm	300mm	1	Black Grey
20630-116	47U	2200mm	600mm	1200mm	1	Black Grey
20630-103	42U	2000mm	600mm	1100mm	1	Black Grey
20630-099	42U	2000mm	600mm	600mm	1	Black Grey

Table 2/2

Katalognummer	Farvekode	Complies With	Frame Material	Type	Works With
20630-118	RAL 7021		Stål	Standard	Varistar CP
20630-067	RAL 7021		Stål	Standard	Varistar CP
20630-091	RAL 7021		Stål	Standard	Varistar CP
20630-120	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-084	RAL 7021		Stål	Standard	Varistar CP
20630-126	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-092	RAL 7021		Stål	Standard	Varistar CP
20630-119	RAL 7021		Stål	Standard	Varistar CP
20630-125	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP

Katalognummer	Farvekode	Complies With	Frame Material	Type	Works With
20630-075	RAL 7021		Stål	Standard	Varistar CP
20630-089	RAL 7021		Stål	Standard	Varistar CP
20630-072	RAL 7021		Stål	Standard	Varistar CP
20630-117	RAL 7021		Stål	Standard	Varistar CP
20630-095	RAL 7021		Stål	Standard	Varistar CP
20630-128	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-114	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-096	RAL 7021		Stål	Standard	Varistar CP
20630-124	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-079	RAL 7021		Stål	Standard	Varistar CP
20630-093	RAL 7021		Stål	Standard	Varistar CP
20630-087	RAL 7021		Stål	Standard	Varistar CP
20630-074	RAL 7021		Stål	Standard	Varistar CP
20630-094	RAL 7021		Stål	Standard	Varistar CP
20630-077	RAL 7021		Stål	Standard	Varistar CP
20630-073	RAL 7021		Stål	Standard	Varistar CP
20630-076	RAL 7021		Stål	Standard	Varistar CP
20630-122	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-101	RAL 7021		Stål	Standard	Varistar CP
20630-097	RAL 7021		Stål	Standard	Varistar CP
20630-090	RAL 7021		Stål	Standard	Varistar CP
20630-088	RAL 7021		Stål	Standard	Varistar CP
20630-098	RAL 7021		Stål	Standard	Varistar CP
20630-068	RAL 7021		Stål	Standard	Varistar CP
20630-078	RAL 7021		Stål	Standard	Varistar CP
20630-123	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-112	RAL 7021		Stål	Standard	Varistar CP
20630-102	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-085	RAL 7021		Stål	Standard	Varistar CP
20630-065	RAL 7021		Stål	Standard	Varistar CP

Katalognummer	Farvekode	Complies With	Frame Material	Type	Works With
20630-110	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-083	RAL 7021		Stål	Standard	Varistar CP
20630-105	RAL 7021		Stål	Standard	Varistar CP
20630-109	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-082	RAL 7021		Stål	Standard	Varistar CP
20630-106	RAL 7021		Stål	Standard	Varistar CP
20630-100	RAL 7021		Stål	Standard	Varistar CP
20630-086	RAL 7021		Stål	Standard	Varistar CP
20630-107	RAL 7021		Stål	Standard	Varistar CP
20630-066	RAL 7021		Stål	Standard	Varistar CP
20630-104	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-080	RAL 7021		Stål	Standard	Varistar CP
20630-108	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-081	RAL 7021		Stål	Standard	Varistar CP
20630-127	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-071	RAL 7021		Stål	Standard	Varistar CP
20630-261	RAL 7021		Stål	Standard	Varistar CP
20630-111	RAL 7021		Stål	Standard	Varistar CP
20630-115	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-113	RAL 7021		Stål	Standard	Varistar CP
20630-121	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-262	RAL 7021		Stål	Standard	Varistar CP
20630-116	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-103	RAL 7021	IEC 61587-1, IEC 61587-3	Stål	Standard	Varistar CP
20630-099	RAL 7021		Stål	Standard	Varistar CP

YDERLIGERE PRODUKTOPLYSNINGER

Castor can be added to the frame. If you will need a castor for your application, you can order a mobile frame which include castors.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden unndladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE