

Varistar CP Mobile Base/Plinth



Mobile base/plinth to make a cabinet mobile.

FUNKTIONER

Covers, St, 1.5 mm

Load-carrying capacity on casters 400 kg, on adjustable feet 1600 kg

Support, St, 3 mm

Color RAL 7021

Plinth height H = 103 mm, with feet adjustable from 126 to 134 mm

SPECIFIKATIONER

Product Type: Cabinet/Rack Base

Materiale: Stål

Table 1/2

Katalognummer	Bredde	Dybde	Pakke mængde	Farve	Farvekode	Finish
21630-664	800mm	1000mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
21630-655	600mm	600mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
21630-663	800mm	900mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
21630-662	800mm	800mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
21630-661	800mm	600mm	1			Struktur Pulvermaling
21630-658	600mm	1000mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
21630-657	600mm	900mm	1	Black Grey	RAL 7021	Struktur Pulvermaling
21630-656	600mm	800mm	1	Black Grey	RAL 7021	Struktur Pulvermaling

Table 2/2

Katalognummer	Type	Works With
21630-664	Base Plinth, Mobile	Varistar CP
21630-655	Base Plinth, Mobile	Varistar CP
21630-663	Base Plinth, Mobile	Varistar CP
21630-662	Base Plinth, Mobile	Varistar CP
21630-661	Base Plinth, Mobile	Varistar CP
21630-658	Base Plinth, Mobile	Varistar CP
21630-657	Base Plinth, Mobile	Varistar CP
21630-656	Base Plinth, Mobile	Varistar CP

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE