

Varistar CP Seismic Base/Plinth

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.



FUNKTIONER

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

SPECIFIKATIONER

Static Load: 400kg
Product Type: Cabinet/Rack Base
Materiale: Stål

Table 1/2

Katalognummer	Bredde	Dybde	Pakke mængde	Farve	Farvekode	Complies With
21630-112	600mm	1000mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-110	600mm	600mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-113	600mm	1200mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-117	800mm	1200mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2

Katalognummer	Bredde	Dybde	Pakke mængde	Farve	Farvekode	Complies With
21630-114	800mm	600mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-116	800mm	1000mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-111	600mm	800mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-115	800mm	800mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2

Table 2/2

Katalognummer	Finish	Højde	Type	Works With
21630-112	Struktur Pulvermaling	103mm	Base Plinth	Varistar CP
21630-110	Struktur Pulvermaling	103mm	Base Plinth	Varistar CP
21630-113	Struktur Pulvermaling	103mm	Base Plinth	Varistar CP
21630-117	Struktur Pulvermaling	103mm	Base Plinth	Varistar CP
21630-114	Struktur Pulvermaling	103mm	Base Plinth	Varistar CP
21630-116	Struktur Pulvermaling	800mm	Base Plinth	Varistar CP
21630-111	Struktur Pulvermaling	103mm	Base Plinth	Varistar CP
21630-115	Struktur Pulvermaling	103mm	Base Plinth	Varistar CP

YDERLIGERE PRODUKTOPLYSNINGER

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE