

Varistar CP Server Cabinet



Welded steel frame for high static load requirements.
Prepared for 19" integration of IT assets.

FUNKTIONER

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg, dynamic 1000 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

SPECIFIKATIONER

Static Load:	1600kg
Product Type:	Rack
Cladding Color Code:	RAL 7021
Frame Material:	Stål

Table 1/2

Katalognummer	Rack Height	Højde	Cladding Material	Bredde	Cladding Color	Dybde
10630-019	47U	2200mm	Stål	600mm	Black Grey	1200mm
10630-017	42U	2000mm	Stål	600mm	Black Grey	1200mm
10630-026	47U	2200mm	Stål	800mm	Black Grey	1200mm

Katalognummer	Rack Height	Højde	Cladding Material	Bredde	Cladding Color	Dybde
10630-023	42U	2000mm	Stål	600mm	Black Grey	1200mm
10630-018	42U	2000mm	Stål	800mm	Black Grey	1200mm
10630-020	47U	2200mm	Stål	800mm	Black Grey	1200mm
10630-024	42U	2000mm	Stål	800mm	Black Grey	1200mm
10630-025	47U	2200mm	Stål	600mm	Black Grey	1200mm

Table 2/2

Katalognummer	Type	Pakke mængde	Dynamic Load	Finish	Materiale
10630-019	Standard	1	1000kgf	Struktur Pulvermaling	Stål
10630-017	Standard	1	1000kgf	Struktur Pulvermaling	Stål
10630-026	Side-by-Side	1	1000kgf	Struktur Pulvermaling	Stål
10630-023	Side-by-Side	1	1000kgf	Struktur Pulvermaling	Stål
10630-018	Standard	1	1000kgf	Struktur Pulvermaling	Stål
10630-020	Standard	1	1000kgf	Struktur Pulvermaling	Stål
10630-024	Side-by-Side	1	1000kgf	Struktur Pulvermaling	Stål
10630-025	Side-by-Side	1	1000kgf	Struktur Pulvermaling	Stål

ADVARSEL

nVent-produkter skal kun installeres og anvendes som angivet i nVents produktvejledninger og træningsmaterialer. Vejledninger er tilgængelige på www.nvent.com og hos din nVent kundeservicerepræsentant. Forkert installation, misbrug, fejlanvendelse eller anden undladelse af fuldt ud at følge nVents instruktioner og advarsler kan medføre funktionsfejl, materielle skader, alvorlige personskader eller død og/eller ugyldiggøre din garanti.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



Vores kraftfulde portefølje af mærker:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE